

# Lab chemicals

---



### Acids, High Purity

- Acetic
- Hydrochloric
- Hydrofluoric
- Nitric
- Phosphoric
- Sulfuric

### Acids, ACS Grade

- Formic
- Nitric
- Perchloric
- Phosphoric
- Sulfuric
- Trifluoroacetic (TFA)

### Buffers, Reference

- Clear pH 4, pH 7, pH 10, and others
- Color-Coded Buffers
- Ion Strength Adjustment (ISAB)
- Phosphate, for BOD
- Total Ionic Strength (TISAB)
- Water Hardness Buffer

### Mobile Analytics

- Ion-Specific Tests
- pH Indicator Papers
- pH Test Strips
- Reflectometry
- Sanitizer Test Kits
- Total Hardness

### Salts, ACS Grade

- Ammonium Nitrate
- Calcium Carbonate
- Potassium Iodide
- Silver Nitrate
- Sodium Chloride
- Sodium Hydroxide

### Solutions: Normal, Molar & %

- EDTA
- Formalin
- Hydrochloric Acid
- Potassium Hydroxide
- Potassium Iodide
- Sodium Hydroxide

### Solvents, ACS Grade

- Acetone
- Chloroform
- Ethanol
- Ethyl Ether
- Isopropanol (IPA)
- Methanol

### Solvents, High Purity

- Acetonitrile
- Dichloromethane (DCM)
- Hexane
- Methanol
- Tetrahydrofuran (THF)
- Water

### Solvents, HPLC Grade

- Acetonitrile
- Dichloromethane (DCM)
- Dimethylformamide (DMF)
- Ethyl Acetate
- Heptane
- Hexane
- Isopropanol (IPA)
- Methanol
- Tetrahydrofuran (THF)
- Toluene
- Water

### Standards, Organic & Inorganic

- Conductivity
- Fluoride (EPA/APHA)
- Ion Chromatography
- Multi-Element Sets, for AA/ICP
- Pesticide (EPA Methods)
- Single Element, for AA/ICP
- Total Organic Carbon (TOC)